



DUO-LOCK extension, cylindrical, steel, short Plain shank, DUO-LOCK interface: DL12



Order data

| | |
|--------------|---------------|
| Order number | 220372 DL12 |
| GTIN | 4034221149893 |
| Item class | 26Y |

Description

Version:

Coated for optimum shrinking in and out.

Technical description

| | |
|------------------------|--------------------------|
| Ø D ₂ | 11.5 mm |
| Overall length L | 60 mm |
| L ₂ | 6 mm |
| Recommended torque | 30 Nm |
| Shank Ø D _s | 12 mm |
| DUO-LOCK interface | DL12 |
| Through-coolant | yes |
| Type of product | Threaded copy mill arbor |