

**DUO-LOCK extension, conical, steel, short SAFE-LOCK, DUO-LOCK interface /  
Ø DS: DL12/20****Order data**

Order number	220376 DL12/20
GTIN	4034221150004
Item class	26Y

**Description****Version:**

Coated for optimum shrinking in and out.

**Technical description**

Overall length L	105 mm
Ø D <sub>2</sub>	11.5 mm
Recommended torque	30 Nm
Shank Ø D <sub>s</sub>	20 mm
DUO-LOCK interface	DL12
Through-coolant	yes
Type of product	Threaded copy mill arbor