

**DUO-LOCK extension, conical, steel, short SAFE-LOCK, DUO-LOCK interface /
Ø DS: DL20/25****Order data**

Order number	220376 DL20/25
GTIN	4034221150127
Item class	26Y

Description**Version:**

Coated for optimum shrinking in and out.

Technical description

Ø D ₂	19.3 mm
Overall length L	95 mm
Shank Ø D _s	25 mm
Recommended torque	80 Nm
DUO-LOCK interface	DL20
Through-coolant	yes
Type of product	Threaded copy mill arbor