

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL12/16****Order data**

Order number	220378 DL12/16
GTIN	4034221149978
Item class	26Y

Description**Version:**

Coated for optimum shrinking in and out.

Technical description

Shank Ø D _s	16 mm
Overall length L	160 mm
DUO-LOCK interface	DL12
Recommended torque	30 Nm
Ø D ₂	11.5 mm
Through-coolant	yes
Type of product	Threaded copy mill arbor