

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL16/20****Order data**

|              |                |
|--------------|----------------|
| Order number | 220378 DL16/20 |
| GTIN         | 4034221150080  |
| Item class   | 26Y            |

**Description****Version:**

Coated for optimum shrinking in and out.

**Technical description**

|                        |                          |
|------------------------|--------------------------|
| Overall length L       | 200 mm                   |
| Ø D <sub>2</sub>       | 15.5 mm                  |
| Recommended torque     | 60 Nm                    |
| Shank Ø D <sub>s</sub> | 20 mm                    |
| DUO-LOCK interface     | DL16                     |
| Through-coolant        | yes                      |
| Type of product        | Threaded copy mill arbor |