

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL10/12****Order data**

Order number	220378 DL10/12
GTIN	4034221149916
Item class	26Y

Description**Version:**

Coated for optimum shrinking in and out.

Technical description

Overall length L	120 mm
Ø D ₂	9.6 mm
Recommended torque	20 Nm
DUO-LOCK interface	DL10
Shank Ø D _s	12 mm
Through-coolant	yes
Type of product	Threaded copy mill arbor