

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL20/25****Order data**

Order number	220378 DL20/25
GTIN	4034221150189
Item class	26Y

**Description****Version:**

Coated for optimum shrinking in and out.

**Technical description**

Overall length L	250 mm
DUO-LOCK interface	DL20
Ø D <sub>2</sub>	19.3 mm
Recommended torque	80 Nm
Shank Ø D <sub>s</sub>	25 mm
Through-coolant	yes
Type of product	Threaded copy mill arbor