

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL10/16****Order data**

Order number	220378 DL10/16
GTIN	4034221149961
Item class	26Y

Description**Version:**

Coated for optimum shrinking in and out.

Technical description

Ø D ₂	9.6 mm
Overall length L	160 mm
Shank Ø D _s	16 mm
Recommended torque	20 Nm
DUO-LOCK interface	DL10
Through-coolant	yes
Type of product	Threaded copy mill arbor