

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL10/20****Order data**

Order number	220378 DL10/20
GTIN	4034221150059
Item class	26Y

Description**Version:**

Coated for optimum shrinking in and out.

Technical description

Ø D ₂	9.6 mm
DUO-LOCK interface	DL10
Overall length L	200 mm
Shank Ø D _s	20 mm
Recommended torque	20 Nm
Through-coolant	yes
Type of product	Threaded copy mill arbor