

**DUO-LOCK extension, conical, steel, long Plain shank, DUO-LOCK interface / Ø DS: DL12/20****Order data**

Order number	220378 DL12/20
GTIN	4034221150073
Item class	26Y

**Description****Version:**

Coated for optimum shrinking in and out.

**Technical description**

Overall length L	200 mm
Recommended torque	30 Nm
DUO-LOCK interface	DL12
Ø D <sub>2</sub>	11.5 mm
Shank Ø D <sub>s</sub>	20 mm
Through-coolant	yes
Type of product	Threaded copy mill arbor