



## DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL20



### Order data

Order number	220375 DL20
GTIN	4034221176769
Item class	10N

### Description

#### Version:

Special dimensions available on request.

### Technical description

Overall length L	125 mm
L <sub>2</sub>	75 mm
Ø D <sub>2</sub>	19.3 mm
Shank Ø D <sub>s</sub>	20 mm
Recommended torque	80 Nm
DUO-LOCK interface	DL20
Through-coolant	yes
Type of product	Threaded copy mill arbor