



## DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL10



### Order data

Order number	220375 DL10
GTIN	4034221176707
Item class	10N

### Description

#### Version:

Special dimensions available on request.

### Technical description

Ø D <sub>2</sub>	9.6 mm
L <sub>2</sub>	37.5 mm
Overall length L	77.5 mm
Recommended torque	20 Nm
Shank Ø D <sub>s</sub>	10 mm
DUO-LOCK interface	DL10
Through-coolant	yes
Type of product	Threaded copy mill arbor