



DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL12



Order data

Order number	220375 DL12
GTIN	4034221176721
Item class	10N

Description

Version:

Special dimensions available on request.

Technical description

Ø D ₂	11.5 mm
Overall length L	93 mm
L ₂	45 mm
Recommended torque	30 Nm
Shank Ø D _s	12 mm
DUO-LOCK interface	DL12
Through-coolant	yes
Type of product	Threaded copy mill arbor