



DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL16



Order data

Order number	220375 DL16
GTIN	4034221176745
Item class	10N

Description

Version:

Special dimensions available on request.

Technical description

L ₂	60 mm
Overall length L	108 mm
Ø D ₂	15.5 mm
Shank Ø D _s	16 mm
Recommended torque	60 Nm
DUO-LOCK interface	DL16
Through-coolant	yes
Type of product	Threaded copy mill arbor