

**Stackable transport boxes with fixed sides, Usable depth × usable width:  
1200X1000mm****Order data**

Order number	963560 1200X1000
GTIN	4251572702755
Item class	96l

**Description****Version:**

Sturdy stackable transport boxes made from sheet metal with W-post design and angled support. With sturdy folded wall section similar to pipes at the top, sturdy round beading in the wall and floor area as well as dimpled label field for freight stickers (freight stickers can be easily removed from the raised dimpled area). Sturdy stacking and attachment brackets with lifting eyes. Large containers can be lifted by crane using certified crane crossbar in vertical pull chains with hooks. Access height 100 mm.

Solid sides.

**Colour:**

Mouse grey RAL 7005.

**Note:**

Also available in the colours fire red RAL 3000, reseda green RAL 6011 and gentian blue RAL 5010. Please contact us.

**Technical description**

Wall version	solid side
Drive-in width	860 mm
Safe working load	2000 kg
mixed stacking of different sizes is possible.	no

Stacking edge on 3 sides	no
Width	1060 mm
Attachment brackets with lifting eyes	yes
Pass-under height	100 mm
stackable	yes
Stackable load	10000 kg
Stacking height maximum	600 mm
Capacity	500 mm
can be lifted by crane	yes
Weight	60 kg
Height	670 mm
Drive-in depth	1060 mm
Material	Sheet metal
Depth	1260 mm
with fork insertion slots	no
Colour	mouse grey RAL 7005
Usable depth	1200 mm
Usable width	1000 mm
Type of product	Transport and stacking large container