

Stackable transport boxes with drop-down side, Usable depth × usable width: 1000X800mm**Order data**

Order number	963561 1000X800
GTIN	4251572701659
Item class	96l

Description**Version:**

Sturdy stackable transport boxes made from sheet metal with W-post design and angled support. With sturdy folded wall section similar to pipes at the top, sturdy round beading in the wall and floor area as well as dimpled label field for freight stickers (freight stickers can be easily removed from the raised dimpled area). Sturdy stacking and attachment brackets with lifting eyes. Large containers can be lifted by crane using certified crane crossbar in vertical pull chains with hooks. Access height 100 mm.

With drop-down side.

Colour:

Mouse grey RAL 7005.

Note:

Also available in the colours fire red RAL 3000, reseda green RAL 6011 and gentian blue RAL 5010. Please contact us.

Technical description

Stacking height maximum	600 mm
Weight	42 kg
Height	670 mm
mixed stacking of different sizes is possible.	no

Attachment brackets with lifting eyes	yes
Depth	1060 mm
Capacity	500 mm
Wall version	with drop-down side
Safe working load	1000 kg
Material	Sheet metal
stackable	yes
can be lifted by crane	yes
Stacking edge on 3 sides	no
Colour	mouse grey RAL 7005
Stackable load	5000 kg
Drive-in width	660 mm
Width	860 mm
Drive-in depth	860 mm
Pass-under height	100 mm
with fork insertion slots	no
Usable width	800 mm
Usable depth	1000 mm
Type of product	Transport and stacking large container