

**Stackable transport boxes with drop-down side, Usable depth × usable width:
800X500mm****Order data**

Order number	963561 800X500
GTIN	4251572701604
Item class	96l

Description**Version:**

Sturdy stackable transport boxes made from sheet metal with W-post design and angled support. With sturdy folded wall section similar to pipes at the top, sturdy round beading in the wall and floor area as well as dimpled label field for freight stickers (freight stickers can be easily removed from the raised dimpled area). Sturdy stacking and attachment brackets with lifting eyes. Large containers can be lifted by crane using certified crane crossbar in vertical pull chains with hooks. Access height 100 mm.

With drop-down side.

Colour:

Mouse grey RAL 7005.

Note:

Also available in the colours fire red RAL 3000, reseda green RAL 6011 and gentian blue RAL 5010. Please contact us.

Technical description

mixed stacking of different sizes is possible.	no
Weight	27 kg
Safe working load	1000 kg
Material	Sheet metal

Colour	mouse grey RAL 7005
Drive-in depth	660 mm
Height	570 mm
can be lifted by crane	yes
Attachment brackets with lifting eyes	yes
Capacity	400 mm
Stacking height maximum	500 mm
with fork insertion slots	no
Depth	860 mm
Drive-in width	360 mm
Width	560 mm
Stackable load	5000 kg
stackable	yes
Stacking edge on 3 sides	no
Pass-under height	100 mm
Wall version	with drop-down side
Usable width	500 mm
Usable depth	800 mm
Type of product	Transport and stacking large container