



Mono grooving toolholder, cranked for face grooving, right-hand, Ø range Groove D1 / D2: 65/100mm



Order data

| | |
|--------------|---------------|
| Order number | 278055 65/100 |
| GTIN | 4062406840389 |
| Item class | 22B |

Description

Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm).
For grooving inserts No. 278029 – 278036.

Note:

D_1 = minimum Ø for the first groove / D_2 = maximum Ø for the first cut.
 $D_2 = 999$ in the size designation corresponds to theoretically infinite.

Technical description

| | |
|---------------------------------|------------|
| maximum cutting depth t_{max} | 14 mm |
| Shank width b | 25×25 mm |
| Screw | 279816 4 |
| Application type | right-hand |
| Through-coolant | no |
| Groove width w | 3; 4 mm |
| Type of product | Cartridges |

