



Mono grooving toolholder, cranked for face grooving, left-hand, Ø range Groove D1 / D2: 160/250mm



Order data

Order number	278054 160/250
GTIN	4062406840334
Item class	22B

Description

Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm).
For grooving inserts No. 278029 – 278036.

Note:

D_1 = minimum Ø for the first groove / D_2 = maximum Ø for the first cut.
 $D_2 = 999$ in the size designation corresponds to theoretically infinite.

Technical description

Shank width b	20×20 mm
maximum cutting depth t_{max}	14 mm
Screw	279816 4
Application type	left-hand
Through-coolant	no
Groove width w	3; 4 mm
Type of product	Cartridges

