



Flat-head angle grinder Cordless, Type: 4933478438



Order data

Order number	077139 4933478438
GTIN	4058546346294
Item class	03L

Description

Version:

Powerful M18 FUEL™ **flat head** angle grinder for working in restricted spaces.

- **Flat head design permits working at angles up to 42°.**
- **Integral FIXTEC quick-release clamping nut for changing discs without using tools.**
- **RAPIDSTOP™ for quick braking of the disc in less than 2 seconds.**
- **Restart inhibit and kick-back stop for high user protection.**

Supplied with:

Without rechargeable batteries or charger. Comes with anti-vibration handle, safety guard, dust-protection grille, clamping set and HD box.

Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

Technical description

Type of rechargeable battery	Lithium-ion
Soft start	yes
Number of rechargeable batteries contained	0
Power supply	Mains operated
Weight	2.6 kg
maximum disc Ø	125 mm
Overload protection	yes

Manufacturer's designation	M18FSAGF125XB-OX
maximum speed	8500 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Restart block	yes
Battery voltage	18 V
Kick-back stop	yes
Dead man's circuit	no
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN	4.86 m/s ²
Type of product	Angle grinder