



## Angle grinder Cordless, Type: 4933478437



### Order data

Order number	077143 4933478437
GTIN	4058546346287
Item class	03L

### Description

#### Version:

Compact M18 FUEL™ cordless angle grinder with **controllable speed**.

- **5 speed settings for the best results when machining stainless steel and aluminium as well as rust and paint removal.**
- **RAPIDSTOP™ for quick braking of the disc in less than 2 seconds for high user protection.**
- **Safety switch cannot be locked for high user protection.**

Version with **dead man's switch** for high user safety.

#### Supplied with:

**Without rechargeable batteries or charger.** Comes with anti-vibration handle, safety guard, dust-protection grille, clamping set and HD box.

#### Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

### Technical description

Dead man's circuit	yes
Packaging	Modular case (HD=Heavy Duty)
maximum speed	3500 - 8500 min <sup>-1</sup>
Weight	2.7 kg
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0

Soft start	yes
Manufacturer's designation	M18FSAGF125XPDB-OX
maximum cutting depth	33 mm
Kick-back stop	yes
Power supply	Mains operated
maximum vibration to EN	5.01 m/s <sup>2</sup>
Battery voltage	18 V
Overload protection	yes
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
maximum disc Ø	125 mm
Restart block	yes
Type of product	Angle grinder