



## Angle grinder Cordless, Type: 4933478436



### Order data

Order number	077143 4933478436
GTIN	4058546346270
Item class	03L

### Description

#### Version:

Compact M18 FUEL™ cordless angle grinder with **controllable speed**.

- **5 speed settings for the best results when machining stainless steel and aluminium as well as rust and paint removal.**
- **RAPIDSTOP™ for quick braking of the disc in less than 2 seconds for high user protection.**
- **Quick adjustment of the safety guard.**

#### Supplied with:

**Without rechargeable batteries or charger.** Comes with anti-vibration handle, safety guard, dust-protection grille, clamping set and HD box.

#### Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

### Technical description

Restart block	yes
Kick-back stop	yes
Manufacturer's designation	M18FSAGV125XB-OX
Power supply	Mains operated
Overload protection	yes
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V

suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Soft start	yes
maximum vibration to EN	5.01 m/s <sup>2</sup>
maximum speed	3500 - 8500 min <sup>-1</sup>
Dead man's circuit	no
Weight	2.7 kg
Type of rechargeable battery	Lithium-ion
maximum disc Ø	125 mm
Packaging	Modular case (HD=Heavy Duty)
Number of rechargeable batteries contained	0
Battery voltage	18 V
maximum cutting depth	33 mm
Type of product	Angle grinder