

**Angle grinder GWS, Type: 14-125****Order data**

|              |               |
|--------------|---------------|
| Order number | 077109 14-125 |
| GTIN         | 4059952576466 |
| Item class   | 03C           |

**Description****Version:**

Powerful 1400-W motor and longer working life: Maximum productivity thanks to better performance and better robustness.

Outstanding, ergonomic handle circumference: First-class ergonomics thanks to significantly reduced handle circumference.

Kickback control, soft start, restart inhibit, overload protection, vibration damping and speed pre-selection.

**Supplied with:**

Supplied with torsion-resistant protective hood, clamping set, additional handle.

**Technical description**

|                  |                              |
|------------------|------------------------------|
| Speed range      | 11500 min <sup>-1</sup>      |
| Restart block    | yes                          |
| Special features | Kickback Control, soft start |
| Kick-back stop   | yes                          |
| Power supply     | Mains-powered                |
| Packaging        | cardboard                    |
| Nominal voltage  | 230 V                        |
| maximum disc Ø   | 125 mm                       |

|                            |               |
|----------------------------|---------------|
| Manufacturer's designation | GWS 14-125    |
| Connection thread          | M14           |
| AC supply voltage          | 230 V         |
| Weight                     | 2.3 kg        |
| Mains frequency            | 50 Hz         |
| Soft start                 | yes           |
| Power consumption          | 1400 W        |
| Type of product            | Angle grinder |