



Cordless impact wrench / impact driver, Type: M12FID2-2



Order data

Order number	074014 M12FID2-2
GTIN	4058546376710
Item class	03L

Description

Version:

- Robust and powerful FUEL™ cordless impact screwdriver with brushless POWERSTATE™ EC motor.
- Long motor service life and high energy efficiency.
- Sturdy metal gearbox casing and ergonomic central handle with soft-grip coating.
- Battery charge display.
- LED illumination of the working area.
- Reversible, with electronic speed control.
- REDLINK PLUS™ electronics – for unique power management.
- DRIVE CONTROL™ permits quick switching between the available settings with different speeds and torques.

Compact impact wrench (127 mm long) with 1/4 inch HEX bit holder.

Advantage:

FUEL™ top model.

Supplied with:

Supplied with 2× Li-ion high-power batteries, charger, HD box.

Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
maximum screw \varnothing (8.8 - 12.9)	M14
Battery voltage	12 V
Tool arbor size	1/4 in
Number of impacts 2nd stage	0 - 2900 min ⁻¹
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Suitable for material	Steel
Manufacturer's designation	M12 FID2-202X
Battery capacity	2 Ah
Tool arbor drive profile	HEX (E 6.3)
typical application	Strong
Weight	0.9 kg
Power supply	Rechargeable battery-powered
maximum torque 1st step	170 Nm
Number of impacts 3rd stage	0 - 3600 min ⁻¹
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN	1.5 m/s ²
Number of impacts 1st stage	0 - 1700 min ⁻¹
Type of product	Impact wrench

Accessories

Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Li-ion system M12B4 Battery type MB12	073815 MB12
Battery charger Type M1218C	073840 M1218C