



Cordless drill / driver, Type: M12FDD2-6



Order data

| | |
|--------------|------------------|
| Order number | 070210 M12FDD2-6 |
| GTIN | 4058546029920 |
| Item class | 03L |

Description

Version:

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use.

- **Brushless POWERSTATE™ motor for more power and a compact shape (151 mm in length).**
- **REDLINK PLUS™ electronics for intelligent power management and overload protection.**
- **16-step electronic torque limit setting, plus drill steps.**

Advantage:

REDLINK PLUS™ electronics.

Supplied with:

Supplied with 2 pcs. 12 V / 6.0 Ah Li-ion batteries, charger, belt clip, HD box.

Note:

See No. 073814, No. 073815, No. 073829 and No. 073840 for suitable replacement batteries and chargers.

Technical description

| | |
|--|------------------------------|
| maximum twist drill size Ø in wood | 35 mm |
| Motor design | Brushless motor |
| maximum vibration to EN | < 2.5 m/s ² |
| Manufacturer's designation | M12FDD-602X |
| Suitable for material | wood |
| Suitable for material | wood |
| Quick-clamping chuck range | 1.5 - 13 mm |
| maximum twist drill size Ø in steel | 13 mm |
| Type of rechargeable battery | Lithium-ion |
| maximum speed 1st speed | 0 - 450 min ⁻¹ |
| suitable battery - supplier / battery type / voltage | Milwaukee type B 12 V |
| Battery voltage | 12 V |
| maximum speed 2nd speed | 1700 min ⁻¹ |
| Weight | 1.5 kg |
| maximum torque hard | 44 Nm |
| Battery capacity | 6 Ah |
| Packaging | Modular case (HD=Heavy Duty) |
| Number of rechargeable batteries contained | 2 |
| Power supply | Rechargeable battery-powered |
| typical application | Strong |
| Type of product | Drill/driver |

Accessories

| | |
|--|---------------|
| Battery charger Type M1218C | 073840 M1218C |
| Offset screwdriving attachment Type OSD2 | 073920 OSD2 |
| Offset screwdriving attachment Type WB1 | 073920 WB1 |
| Li-ion system M12B6 Battery type MB12 | 073829 MB12 |

Battery charger Type M1218FC

073840 M1218FC