



FlyMarker® mini 120/45 needle marker Cordless, Battery capacity: 2X8



Order data

Order number	085753 2X8
GTIN	
Item class	04F

Description

Version:

For permanent identification / marking / lettering of batch and series production parts of different materials (steel, stainless steel, aluminium, copper, brass, plastics, tool steel, hardened steels up to 62 HRC, etc.).

- Powerful electro-magnetic marking needle drive.
- Simple intuitive software with password protection and newly designed parameter display for a quick insight into any programme line
- Large 4.3 inch colour display
- Latest processor technology for smooth menu navigation and a very short boot time.
- 1:1 preview of the marking field in the display.
- Casing made of break-proof and glass fibre-reinforced plastic.
- Interfaces: USB-A, USB-B and Ethernet.
- Font: Dot matrix in a 5×7 or 9×13 grid, font height 1.0 – 10.0 mm and larger.
- Font for a character height greater than 10.0 mm on request.
- High-quality double linear guides for precise marking results.
- Round parts can be marked radially and axially, and also in an arc of a circle.

Extremely handy 100% mobile **cordless manual marking system** with touch user interface and large 4.3 inch colour display.

Supplied with:

Including tool kit, solid carbide marking needle 90°. Adjustment bracket with non-slip coating, setting gauge, and carrying case, **2 pcs. 18 V Li-ion batteries**, charger.

Technical description

Character height	1 - 10 mm
Battery capacity	8 Ah
Nominal voltage	18 V
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Power supply	Mains operated
Interface	USB interface
maximum marker field width	120 mm
maximum marker field height	45 mm
Type of product	Needle marker