

**Carbide-tipped hammer drill SDS-plus "7X", Ø×overall length: 12X215mm****Order data**

Order number	789058 12X215
GTIN	4059952531823
Item class	76K

Description**Version:**

New generation **EXPERT SDS-Plus "7X"** with welded 4-edge solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **2+2 flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Technical description

Flute length	150 mm
overall length	215 mm
Number of cutting edges Z	4
Ø	12 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill