



Carbide-tipped hammer drill SDS-plus "7X", Øxoverall length: 5X115mm



Order data

| | |
|--------------|---------------|
| Order number | 789058 5X115 |
| GTIN | 4059952531328 |
| Item class | 76K |

Description

Version:

New generation **EXPERT SDS-Plus "7X"** with welded 4-edge solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **2+2 flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Technical description

| | |
|----------------------------------|-----------------|
| Flute length | 50 mm |
| Number of cutting edges Z | 4 |
| Ø | 5 mm |
| overall length | 115 mm |
| Tool material | Carbide |
| Use with impact / without impact | Impact drilling |
| Shank | SDS Plus |
| Type of product | Masonry drill |