



## Carbide-tipped hammer drill SDS-plus "7X", Øxoverall length: 20X450mm



### Order data

Order number	789058 20X450
GTIN	4059952532165
Item class	76K

### Description

#### Version:

New generation **EXPERT SDS-Plus "7X"** with welded 4-edge solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

#### Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **2+2 flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

### Technical description

Flute length	400 mm
overall length	450 mm
Number of cutting edges Z	4
Ø	20 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill