



Carbide-tipped hammer drill SDS-max "8X", Ø×overall length: 32X520mm



Order data

Order number	789206 32X520
GTIN	4059952533292
Item class	76K

Description

Version:

New generation **EXPERT SDS-max "8X"** with welded 4-edge solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

Special carbide insert geometry for longer tool lives.

Drill head with square cross section from Ø 16 mm.

Application:

For drilling concrete, natural stone, and masonry.

Note:

Generation SDS-max-7 drill (with embedded carbide cutting edges, soldered) in the size 35×520 – 52×520 under No. 789204.

Technical description

Flute length	400 mm
Ø	32 mm
overall length	520 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

