

**Carbide-tipped hammer drill SDS-max "8X", Ø×overall length: 25X520mm****Order data**

Order number	789206 25X520
GTIN	4059952533155
Item class	76K

Description**Version:**

New generation **EXPERT SDS-max "8X"** with welded 4-edge solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

Special carbide insert geometry for longer tool lives.

Drill head with square cross section from Ø 16 mm.

Application:

For drilling concrete, natural stone, and masonry.

Note:

Generation SDS-max-7 drill (with embedded carbide cutting edges, soldered) in the size 35×520 – 52×520 under No. 789204.

Technical description

overall length	520 mm
Flute length	400 mm
Ø	25 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

