

**Carbide-tipped hammer drill SDS-max "8X", Ø×overall length: 22X320mm****Order data**

Order number	789206 22X320
GTIN	4059952533070
Item class	76K

**Description****Version:**

New generation **EXPERT SDS-max "8X"** with welded 4-edge solid carbide head. Shaped cutters for high drilling performance, long working life and low wear. No digging in when drilling in reinforced concrete.

**Special carbide insert geometry for longer tool lives.**

Drill head with square cross section from Ø 16 mm.

**Application:**

For drilling concrete, natural stone, and masonry.

**Note:**

Generation SDS-max-7 drill (with embedded carbide cutting edges, soldered) in the size 35×520 – 52×520 under No. 789204.

**Technical description**

Ø	22 mm
overall length	320 mm
Flute length	200 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Max
Type of product	Masonry drill

