

ELTEN**Shoe, grey VINTAGE Low ESD, S3, EU shoe size: 40**

Order data

Order number	092230 40
GTIN	4030839220344
Item class	09P

Description

Version:

Modern safety shoes in vintage design.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining, BIOACTIVE for a pleasant foot climate.**
- **Padded tongue.**
- **ESD PRO grey full-size insole.**
- **L10 TPU/PU sole, anti-slip.**
- **ESD security.**

Safety shoe with bioactive inner lining. Particularly **gentle to the skin and odour-suppressant**.
Extra laces supplied (grey).

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Supplied with:

With extra laces in grey.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 37 – 48.

Technical description

Colour	grey
--------	------

Material inner lining	breathable textile inner lining
Standard	Inlay type-tested according to DGUV regulation 191
The entire shoe is waterproof	yes
Closure	Laces
anti-static	yes
Material of outer sole	TPU-/PU
EU shoe size	40
suitable for orthopaedic insoles	yes
oil- and petrol-resistant sole	yes
Uppers material	Genuine leather
Puncture resistance	Textile
Material of protective toe-cap	Steel
Shoe type	Low shoe
Energy absorption in the heel area	yes
Slip resistance	yes
against water penetration and water absorption	yes
Protection class	S3
Series	VINTAGE
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes