

Frame type S610-M18-U, Depth 1100 mm, Height: 5000mm**Order data**

Order number	991322 5000
GTIN	4058255104321
Item class	96P

Description**Version:**

Frame profiles with framework stiffening. Solid base plates transmit the load to the floor. Supplied with 4 floor anchors and 2 shim plates 2 mm per frame.

Description:**Extension size:****Overall length of the rack:**

For frame stiles S610-M18-U: Nominal length + number of stiles × 86 mm.

Suitable for:

Pallet racking from build year 08/2018.

Colour:

Similar to RAL 5017 traffic blue, **powder-coated**.

Note:

The load capacities required for the racking bay determine the frame type. See load table for details.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

For racks up to build year 05/2022, cross beams may only be used as a replacement in the event of damage. If the rack is changed, e.g. installation of additional cross beam levels, recalculation must be performed as per DIN EN 15512:2020.

Technical description

Application range	Pallet racking
Depth	1100 mm
Frame profile type	S610-M18-U
Height	5000 mm
Product name attribute	Depth 1100 mm
Type of product	Column frame