

**Frame type S610-M18-U, Depth 1100 mm, Height: 3500mm****Order data**

Order number	991322 3500
GTIN	4058255104291
Item class	96P

**Description****Version:**

Frame profiles with framework stiffening. Solid base plates transmit the load to the floor. Supplied with 4 floor anchors and 2 shim plates 2 mm per frame.

**Description:****Extension size:****Overall length of the rack:**

For frame stiles S610-M18-U: Nominal length + number of stiles × 86 mm.

**Suitable for:**

Pallet racking from build year 08/2018.

**Colour:**

Similar to RAL 5017 traffic blue, **powder-coated**.

**Note:**

The load capacities required for the racking bay determine the frame type. See load table for details.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

For racks up to build year 05/2022, cross beams may only be used as a replacement in the event of damage. If the rack is changed, e.g. installation of additional cross beam levels, recalculation must be performed as per DIN EN 15512:2020.

**Technical description**

Frame profile type	S610-M18-U
Application range	Pallet racking
Height	3500 mm
Depth	1100 mm
Product name attribute	Depth 1100 mm
Type of product	Column frame