

Frame type S625-A18, Depth 1100 mm, Height: 3500mm

Order data

Order number	991323 3500
GTIN	4004514287489
Item class	96P

Description**Version:**

Frame profiles with framework stiffening. Solid base plates transmit the load to the floor. Supplied with 4 floor anchors and 2 shim plates 2 mm per frame.

Description:**Extension size:****Overall length of the rack:**

For frame stiles S625-A18 Nominal length + number of stiles × 110 mm.

Suitable for:

Pallet racking from build year 08/2018.

Colour:

Similar to RAL 5017 traffic blue, **powder-coated**.

Note:

The load capacities required for the racking bay determine the frame type. See load table for details.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

For racks up to build year 05/2022, cross beams may only be used as a replacement in the event of damage. If the rack is changed, e.g. installation of additional cross beam levels, recalculation must be performed as per DIN EN 15512:2020.

Technical description

Depth	1100 mm
Frame profile type	S625-A18
Height	3500 mm
Application range	Pallet racking
Product name attribute	Depth 1100 mm
Type of product	Column frame