

## Frame type S625-A18, Depth 1100 mm, Height: 2500mm



### Order data

Order number	991323 2500
GTIN	4058255068920
Item class	96P

### Description

#### Version:

Frame profiles with framework stiffening. Solid base plates transmit the load to the floor. Supplied with 4 floor anchors and 2 shim plates 2 mm per frame.

#### Description:

#### Extension size:

#### Overall length of the rack:

For frame stiles S625-A18 Nominal length + number of stiles × 110 mm.

#### Suitable for:

Pallet racking from build year 08/2018.

#### Colour:

Similar to RAL 5017 traffic blue, **powder-coated**.

#### Note:

The load capacities required for the racking bay determine the frame type. See load table for details.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

For racks up to build year 05/2022, cross beams may only be used as a replacement in the event of damage. If the rack is changed, e.g. installation of additional cross beam levels, recalculation must be performed as per DIN EN 15512:2020.

### Technical description

Height	2500 mm
Frame profile type	S625-A18
Depth	1100 mm
Application range	Pallet racking
Product name attribute	Depth 1100 mm
Type of product	Column frame