



LED torch with rechargeable battery, Type: 130



Order data

Order number	081362 130
GTIN	4062406942571
Item class	02A

Description

Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- **Charging and discharge monitoring by means of coloured LED in the switch.**
- **Long running time with constant light output.**
- **USB-C charging socket.**
- **Anti-roll protection.**
- **With focussable lamp head.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable and battery. With hand loop.

Note:

For suitable replacement batteries see No. 081365

Technical description

Illumination time	1 h
IP Index of Protection	IP 54
Overall length	118 - 130 mm
Illumination	300 lm

Weight	70 g
Number of rechargeable batteries contained	1
Battery capacity	0.9 Ah
Power supply	Rechargeable battery-powered
Illumination step 2	100 lm
Replaceable battery	yes
Battery voltage	3.7 V
Torch function	Focus
Type of rechargeable battery	Lithium-ion
Head Ø	26 mm
Light current boost	450 lm
Illumination time stage 2	2.5 h
Bulb	LED lamp
CRI value	>80
Illumination time boost	30 s
Type of product	Flashlight

Accessories

Replacement battery 14500	081365 14500
---------------------------	--------------