



LED pen torch with rechargeable battery, Type: 120



Order data

Order number	081360 120
GTIN	4062406942557
Item class	02A

Description

Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- **Charging and discharge monitoring by means of coloured LED in the switch.**
- **Long running time with constant light output.**
- **USB-C charging socket.**
- **Anti-roll protection.**
- **With focussable lamp head.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable and battery. With hand loop.

Note:

For suitable replacement batteries see No. 081365

Technical description

Type of rechargeable battery	Lithium-ion
Light current boost	130 lm
Illumination time boost	30 s
Replaceable battery	yes
Head Ø	18 mm

Illumination time	1 h
Battery capacity	0.32 Ah
IP Index of Protection	IP 54
Illumination time stage 2	3 h
Power supply	Rechargeable battery-powered
Bulb	LED lamp
Weight	29.5 g
Overall length	112 - 120 mm
Battery voltage	3.7 V
Illumination	80 lm
Torch function	Focus
Number of rechargeable batteries contained	1
Illumination step 2	30 lm
CRI value	>80
Type of product	Flashlight

Accessories

Replacement battery 10440	081365 10440
---------------------------	--------------