



## LED torch with rechargeable battery, Type: 150



### Order data

Order number	081363 150
GTIN	4062406942588
Item class	02A

### Description

#### Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- **Charging and discharge monitoring by means of coloured LED in the switch.**
- **Long running time with constant light output.**
- **USB-C charging socket.**
- **Anti-roll protection.**
- **With focussable lamp head.**

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with USB-C charging cable and battery. With hand loop.

#### Note:

For suitable replacement batteries see No. 081365

### Technical description

Illumination step 2	140 lm
IP Index of Protection	IP 54
Head Ø	28 mm
Overall length	144 - 154 mm
Power supply	Rechargeable battery-powered

Battery capacity	1.6 Ah
Replaceable battery	yes
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Illumination	400 lm
Torch function	Focus
Illumination time stage 2	5 h
Battery voltage	3.7 V
CRI value	>80
Illumination time	1.5 h
Bulb	LED lamp
Illumination time boost	30 s
Weight	95 g
Light current boost	700 lm
Type of product	Flashlight

---

## Accessories

Replacement battery 16650	081365 16650
---------------------------	--------------