



## LED pen torch with rechargeable battery, Type: 160



### Order data

Order number	081361 160
GTIN	4062406942564
Item class	02A

### Description

#### Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- **Charging and discharge monitoring by means of coloured LED in the switch.**
- **Long running time with constant light output.**
- **USB-C charging socket.**
- **Anti-roll protection.**
- **With focussable lamp head.**

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with USB-C charging cable and battery. With practical pocket clip.

#### Note:

For suitable replacement batteries see No. 081365

### Technical description

Power supply	Rechargeable battery-powered
Illumination step 2	50 lm
Light current boost	250 lm
Illumination time	1 h
Number of rechargeable batteries contained	1

Overall length	154 - 161 mm
Type of rechargeable battery	Lithium-ion
Head Ø	18 mm
Battery voltage	3.7 V
Weight	41 g
Illumination	150 lm
Battery capacity	0.6 Ah
Bulb	LED lamp
IP Index of Protection	IP 54
Illumination time stage 2	3 h
Torch function	Focus
Replaceable battery	yes
CRI value	>80
Illumination time boost	30 s
Type of product	Flashlight

---

## Accessories

Replacement battery 10840	081365 10840
---------------------------	--------------