

AEG

Cordless drill / driver, Type: BS18C3BL4



Order data

Order number	070222 BS18C3BL4
GTIN	4058546362188
Item class	07A

Description

Version:

AEG – Cordless drill / driver

- Sturdy and handy cordless 2-speed drill / screwdriver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.
- LED illumination of the working area.
- 13 mm metal drill chuck.
- 24-step torque adjustment.
- Extremely handy and lightweight.
- Metal gearbox casing

Version of the advertising text:

- Sturdy and handy cordless 2-speed drill / driver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.

Supplied with:

Supplied with 2× 18V / 4.0 Ah PRO Li-ion SHD batteries, charger, belt clip, carrying case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073820 and No. 073846 – No. 073848 for suitable replacement batteries and chargers. Suitable chargers and starter sets can be found under No. 073841 and No 073844.

Technical description

Battery voltage	18 V
Packaging	Carrying case
Weight	5.88 kg
Motor design	Brushless
Number of rechargeable batteries contained	2
maximum twist drill size Ø in wood	65 mm
typical application	Heavy Duty
maximum twist drill size Ø in steel	13 mm
maximum torque hard	110 Nm
Type of rechargeable battery	Lithium-ion
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 1st speed	0 - 500 min ⁻¹
maximum speed 2nd speed	0 - 2100 min ⁻¹
Manufacturer's designation	BS18C3BL-402C
Power supply	Rechargeable battery-powered
Battery capacity	4 Ah
Type of product	Drill/driver
USP1	18V
USP2	FIXTEC quick-change chuck, with softgrip