


**HOLEX****HOLEX CleverDrill HSS jobber drill N, uncoated, Ø DC h8: 5mm****Order data**

Order number	GG4031 5
GTIN	4067263101819
Item class	GGN

**Description****Version:**

**HOLEX CleverDrill:** Sturdy drill for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

**Same as No. 114031.**

**Recommendation:****Maximum drilling depth:**

$$L_2 = L_C - 1.5 \times D_C$$

**Note:**

**Successor product to No. 114030.**

Size 13.5 – 16: With stepped shank Ø 12.7 mm.

**Technical description**

Standard	DIN 338
Number of cutting edges Z	2
Feed f in steel < 750 N/mm <sup>2</sup>	0.05 mm/rev.
Overall length L	86 mm
recommended maximum drilling depth L <sub>2</sub>	44.5 mm
Point angle	118 degrees

Flute length $L_c$	52 mm
Tolerance nominal $\varnothing$	h8
Shank $\varnothing D_s$	5 mm
Shank	Plain shank
Nominal $\varnothing D_c$	5 mm
Contents	20
Series	CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	60 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	35 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	32 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	22 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	18 m/min	P
GG(G)	suitable only under restricted conditions	30 m/min	K
CuZn	suitable	40 m/min	N

Oil	suitable
wet maximum	suitable

## Accessories

HOLEX CleverDrill HSS jobber drillN Ø DC h8 (mm or inch) 5	114031 5
HOLEX CleverDrill jobber drill set HSS No. 114031 in a case Type 1-10	115051 1-10
HOLEX CleverDrill jobber drill set HSS No. 114031 in a case Type 1-10,5	115051 1-10,5
HOLEX CleverDrill jobber drill set HSS No. 114031 in a case Type 1-13	115051 1-13
HOLEX CleverDrill HSS jobber drill set No. 114031 as a refill set Type 1-10	115056 1-10
HOLEX CleverDrill HSS jobber drill set No. 114031 as a refill set Type 1-10,5	115056 1-10,5
HOLEX CleverDrill HSS jobber drill set No. 114031 as a refill set Type 1-13	115056 1-13
HOLEX CleverDrill HSS jobber drill set No. 114031 as a refill set Type 1-6	115056 1-6