



Digital external micrometer, Measuring range: 75-100mm



Order data

Order number	421492 75-100
GTIN	4067263101703
Item class	42B

Description

Version:

Easy-to-read display. Carbide-tipped measuring faces.
Digital and analogue graduations. Dust-proof and splash-proof metal casing.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032. 1 plug-in sphere for measuring curved surfaces. 1 setting standard.

Technical description

Measuring range	75 - 100 mm
Number of batteries contained	1
Spindle pitch	0.5 mm
Power supply	Battery-powered
Scale divisions	0.001 mm
IP Index of Protection	IP 54
Spindle Ø	6.5 mm
Error limit	5 µm
Article no of the battery / rechargeable battery fitted	081560 CR2032

Calibration	B2
Battery type	Button cell
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Micrometer setting standard overall length 75 mm	421100 75