

**Digital external micrometer, Measuring range: 0-25mm****Order data**

Order number	421492 0-25
GTIN	4062406051488
Item class	42B

Description**Version:**

Easy-to-read display. Carbide-tipped measuring faces.
Digital and analogue graduations. Dust-proof and splash-proof metal casing.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032. 1 plug-in sphere for measuring curved surfaces.

Technical description

Error limit	4 µm
Power supply	Battery-powered
Spindle Ø	6.5 mm
Calibration	B1
Number of batteries contained	1
Battery type	Button cell
Spindle pitch	0.5 mm
Scale divisions	0.001 mm
IP Index of Protection	IP 54

Article no of the battery / rechargeable battery fitted	081560 CR2032
Measuring range	0 - 25 mm
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------