



## Digital external micrometer, Measuring range: 50-75mm



### Order data

Order number	421492 50-75
GTIN	4062406063207
Item class	42B

### Description

#### Version:

Easy-to-read display. Carbide-tipped measuring faces.  
Digital and analogue graduations. Dust-proof and splash-proof metal casing.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032. 1 plug-in sphere for measuring curved surfaces. 1 setting standard.

### Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Error limit	5 µm
Battery type	Button cell
Measuring range	50 - 75 mm
Scale divisions	0.001 mm
Calibration	B2
Spindle Ø	6.5 mm
Power supply	Battery-powered

Spindle pitch	0.5 mm
IP Index of Protection	IP 54
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

### Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

### Accessories

Micrometer setting standard overall length 50 mm	421100 50
Button cell / special battery Battery type CR2032	081560 CR2032