

**Digital external micrometer set, Measuring range: 0-100mm****Order data**

| | |
|--------------|---------------|
| Order number | 421496 0-100 |
| GTIN | 4062406063221 |
| Item class | 42B |

Description**Version:**

Easy-to-read display. Carbide-tipped measuring faces.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

External micrometers No. 421492 with appropriate micrometer standards.

Technical description

| | |
|---|-----------------|
| Number of micrometers | 4 |
| Measuring range | 0 - 100 mm |
| Number of batteries contained | 4 |
| IP Index of Protection | IP 54 |
| Number of micrometer standards | 3 |
| Power supply | Battery-powered |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |

| | |
|------------------------|--------------------------|
| Standard | DIN 863 |
| Measurement technology | digital |
| Packaging | sturdy box |
| Calibration | S2 |
| Type of product | External tube micrometer |

Services

| | |
|--|--------------|
| Calibration External micrometer set Measuring range 0-100 mm | 020430 0-100 |
| DAkkS calibration External micrometer set Measuring range 0-100 mm | 020440 0-100 |

Accessories

| | |
|---|---------------|
| Digital external micrometer Measuring range 0-25 mm | 421492 0-25 |
| Digital external micrometer Measuring range 25-50 mm | 421492 25-50 |
| Digital external micrometer Measuring range 50-75 mm | 421492 50-75 |
| Digital external micrometer Measuring range 75-100 mm | 421492 75-100 |
| Button cell / special battery Battery type 357 | 081560 357 |