



Digital external micrometer with offset measuring faces, Measuring range: 0-25mm



Order data

Order number	421721 0-25
GTIN	4062406063238
Item class	42B

Description

Version:

Easy to read digital display with additional analogue reading. Robust metal casing. Rotating measurement spindle, carbide-tipped measuring faces

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Power supply	Battery-powered
Battery type	Button cell
Error limit	4 μ m
Scale divisions	0.00005 in
IP Index of Protection	IP 54
Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Calibration	B1

Number of batteries contained	1
Standard	DIN 863
Measurement technology	digital
Packaging	sturdy box
Reversible reading	mm / inch
Micrometer barrel graduations	1/50
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25

Accessories

Button cell / special battery Battery type 357	081560 357
--	------------