



Digital external micrometer with disc anvils, Measuring range: 0-25mm



Order data

Order number	421729 0-25
GTIN	4062406063269
Item class	42B

Description

Version:

Easy to read digital display with additional analogue reading. Robust metal casing. Stationary measurement spindle

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Parallelism of the measuring faces	4 µm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Calibration	B1
Error limit	4 µm
Battery type	Button cell
Scale divisions	0.00005 in
Disc anvil Ø	20 mm
Power supply	Battery-powered
Scale divisions	0.001 mm
Standard	DIN 863

Measurement technology	digital
Packaging	sturdy box
Reversible reading	mm / inch
Micrometer barrel graduations	1/50
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100

Accessories

Button cell / special battery Battery type 357	081560 357
--	------------