



Digital external micrometer for groove measurement, Measuring range: 0-25mm



Order data

Order number	421725 0-25
GTIN	4062406063245
Item class	42B

Description

Version:

Easy to read digital display with additional analogue reading. Robust metal casing.
Stationary measurement spindle

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Battery type	Button cell
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Scale divisions	0.001 mm
Error limit	4 μ m
Number of batteries contained	1
Calibration	B1
Scale divisions	0.00005 in
Standard	DIN 863
Measurement technology	digital

Packaging	sturdy box
Reversible reading	mm / inch
Micrometer barrel graduations	1/50
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25

Accessories

Button cell / special battery Battery type 357	081560 357
--	------------